

Varistar CP Glazed Door With 3-Point Locking

Power Utilities

Glass door with 3 point locking allows stronger adhesion between door and the cabinet frame. This prevents the metal mealeability to show and provides the door extra robustness.

FEATURES

Glazed Door With 3-Point Locking, With Lock

Lever handle with key insert (2 keys)

Opening angle 180°

Security glass, 6 mm

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Protection Rating	Color	Color Code	Complies With	Finish
21630-092	42 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-093	47 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-094	52 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-095	42 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-096	47 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-097	52 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	

CatalogNumber	Rack Height	Protection Rating	Color	Color Code	Complies With	Finish
21630-416	24 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-417	24 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-418	29 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-419	29 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-420	33 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-421	33 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-422	38 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-423	38 U	IP20	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	
21630-717	24 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-718	24 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-719	29 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-720	29 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-721	33 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-722	33 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-723	38 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-724	38 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-725	42 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-726	42 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated

CatalogNumber	Rack Height	Protection Rating	Color	Color Code	Complies With	Finish
21630-727	47 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-728	47 U	IP55	Black Grey	RAL 7021	IEC 61587-1	Powder Coated

Table 2/2

Catalog Number	Locking Type	Material	Product Type	Type	Works With
21630-092	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-093	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-094	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-095	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-096	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-097	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-416	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-417	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-418	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-419	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-420	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-421	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-422	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-423	3-Point Locking		Cabinet Door	Glass Door	Varistar CP
21630-717	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP

Catalog Number	Locking Type	Material	Product Type	Type	Works With
21630-718	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP
21630-719	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP
21630-720	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP
21630-721	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP
21630-722	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP
21630-723	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP
21630-724	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP
21630-725	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP
21630-726	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP
21630-727	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP
21630-728	3-Point Locking	Steel, Glass	Cabinet Door	Glass Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE