

Varistar CP Steel Door, Perforated With 3-Point Locking

Power Utilities

Varistar CP perforated steel door 3-point locking for IP 20 applications.

FEATURES

Perforated steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Color	Color Code	Complies With	Locking Type	Product Type
21630-098	42 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-099	47 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-100	52 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-101	42 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-102	47 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-103	52 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-424	24 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door

CatalogNumber	Rack Height	Color	Color Code	Complies With	Locking Type	Product Type
21630-425	24 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-426	29 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-427	29 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-428	33 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-429	33 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-430	38 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-431	38 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door

Table 2/2

Catalog Number	Protection Rating	Type	Works With
21630-098	IP20	Steel Door, Perforated	Varistar CP
21630-099	IP20	Steel Door, Perforated	Varistar CP
21630-100	IP20	Steel Door, Perforated	Varistar CP
21630-101	IP20	Steel Door, Perforated	Varistar CP
21630-102	IP20	Steel Door, Perforated	Varistar CP
21630-103	IP20	Steel Door, Perforated	Varistar CP
21630-424	IP20	Steel Door, Perforated	Varistar CP
21630-425	IP20	Steel Door, Perforated	Varistar CP
21630-426	IP20	Steel Door, Perforated	Varistar CP
21630-427	IP20	Steel Door, Perforated	Varistar CP

Catalog Number	Protection Rating	Type	Works With
21630-428	IP20	Steel Door, Perforated	Varistar CP
21630-429	IP20	Steel Door, Perforated	Varistar CP
21630-430	IP20	Steel Door, Perforated	Varistar CP
21630-431	IP20	Steel Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE