

Varistar CP Steel Door, Perforated With Multi-Point Locking

Power Utilities

EMC doors with good contact with the frame and gasket to achieve high attenuation.

The 4 point locking helps achieve necessary contact to avoid EMI effects on electronics.

FEATURES

Perforated door with 4-point locking for EMC applications

Interior galvanized

Opening angle 180°

Lever handle with push button

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Color	Color Code	Locking Type	Material	Product Type
21630-533	24 U	Black Grey	RAL 7021	3-Point Locking	Steel	Cabinet Door
21630-534	24 U	Black Grey	RAL 7021	3-Point Locking	Steel	Cabinet Door
21630-535	29 U	Black Grey	RAL 7021	3-Point Locking	Steel	Cabinet Door
21630-536	29 U	Black Grey	RAL 7021	3-Point Locking	Steel	Cabinet Door
21630-537	33 U	Black Grey	RAL 7021	4-Point Locking	Steel	Cabinet Door
21630-538	33 U	Black Grey	RAL 7021	4-Point Locking	Steel	Cabinet Door
21630-539	38 U	Black Grey	RAL 7021	4-Point Locking	Steel	Cabinet Door

CatalogNumber	Rack Height	Color	Color Code	Locking Type	Material	Product Type
21630-540	38 U	Black Grey	RAL 7021	4-Point Locking	Steel	Cabinet Door
21630-541	42 U	Black Grey	RAL 7021	4-Point Locking	Steel	Cabinet Door
21630-542	42 U	Black Grey	RAL 7021	4-Point Locking	Steel	Cabinet Door
21630-543	47 U	Black Grey	RAL 7021	5-Point Locking	Steel	Cabinet Door
21630-544	47 U	Black Grey	RAL 7021	5-Point Locking	Steel	Cabinet Door

Table 2/2

Catalog Number	Type
21630-533	Steel Door, Perforated
21630-534	Steel Door, Perforated
21630-535	Steel Door, Perforated
21630-536	Steel Door, Perforated
21630-537	Steel Door, Perforated
21630-538	Steel Door, Perforated
21630-539	Steel Door, Perforated
21630-540	Steel Door, Perforated
21630-541	Steel Door, Perforated
21630-542	Steel Door, Perforated
21630-543	Steel Door, Perforated
21630-544	Steel Door, Perforated

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE