

Varistar CP Steel Door, Plain With 1-Point Locking

Power Utilities

Varistar CP Steel Door Single Point Locking for IP 20 applications.

FEATURES

Steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Locking Type	Color	Color Code	Complies With	Product Type
21630-400	24 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-401	24 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-493	24 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door
21630-494	24 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door
21630-402	29 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-403	29 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-495	29 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door
21630-496	29 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door

CatalogNumber	Rack Height	Locking Type	Color	Color Code	Complies With	Product Type
21630-404	33 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-405	33 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-497	33 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door
21630-498	33 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door
21630-406	38 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-407	38 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-499	38 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door
21630-500	38 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door
21630-002	42 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-009	42 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-501	42 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door
21630-502	42 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door
21630-003	47 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-010	47 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-503	47 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door
21630-504	47 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1	Cabinet Door
21630-004	52 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door
21630-011	52 U	Single Point Locking	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	Cabinet Door

Table 2/2

Catalog Number	Protection Rating	Type	Works With
21630-400	IP20	Steel Door	Varistar CP
21630-401	IP20	Steel Door	Varistar CP
21630-493	IP20	Steel Door	Varistar CP
21630-494	IP20	Steel Door	Varistar CP
21630-402	IP20	Steel Door	Varistar CP
21630-403	IP20	Steel Door	Varistar CP
21630-495	IP20	Steel Door	Varistar CP
21630-496	IP20	Steel Door	Varistar CP
21630-404	IP20	Steel Door	Varistar CP
21630-405	IP20	Steel Door	Varistar CP
21630-497	IP20	Steel Door	Varistar CP
21630-498	IP20	Steel Door	Varistar CP
21630-406	IP20	Steel Door	Varistar CP
21630-407	IP20	Steel Door	Varistar CP
21630-499	IP20	Steel Door	Varistar CP
21630-500	IP20	Steel Door	Varistar CP
21630-002	IP20	Steel Door	Varistar CP
21630-009	IP20	Steel Door	Varistar CP

Catalog Number	Protection Rating	Type	Works With
21630-501	IP20	Steel Door	Varistar CP
21630-502	IP20	Steel Door	Varistar CP
21630-003	IP20	Steel Door	Varistar CP
21630-010	IP20	Steel Door	Varistar CP
21630-503	IP20	Steel Door	Varistar CP
21630-504	IP20	Steel Door	Varistar CP
21630-004	IP20	Steel Door	Varistar CP
21630-011	IP20	Steel Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order lever handle with push button separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE