

# Varistar CP Steel Door, Plain With Multi-Point Locking, Shortened

## Power Utilities

EMC and IP55 Steel Door with lever handle and 5-Point locking.

### FEATURES

Height of connection plate 400 mm

Lever handle with push button

Opening angle 180°

Steel door with 5-point locking for EMC applications

### SPECIFICATIONS

Table 1/1

Catalog Number	Rack Height	Protection Rating	Color	Color Code	Locking Type	Product Type
21630-372	38 U	IP55	Black Grey	RAL 7021	3-Point Locking	Cabinet Door
21630-373	38 U	IP55	Black Grey	RAL 7021	3-Point Locking	Cabinet Door
21630-711	38 U	IP55	Black Grey	RAL 7021	3-Point Locking	Cabinet Door
21630-712	38 U	IP55	Black Grey	RAL 7021	3-Point Locking	Cabinet Door
21630-374	42 U	IP55	Black Grey	RAL 7021	4-Point Locking	Cabinet Door
21630-375	42 U	IP55	Black Grey	RAL 7021	4-Point Locking	Cabinet Door
21630-376	47 U	IP55	Black Grey	RAL 7021	4-Point Locking	Cabinet Door

CatalogNumber	Rack Height	Protection Rating	Color	Color Code	Locking Type	Product Type
21630-377	47 U	IP55	Black Grey	RAL 7021	4-Point Locking	Cabinet Door
21630-713	42 U	IP55	Black Grey	RAL 7021	4-Point Locking	Cabinet Door
21630-714	42 U	IP55	Black Grey	RAL 7021	4-Point Locking	Cabinet Door
21630-715	47 U	IP55	Black Grey	RAL 7021	4-Point Locking	Cabinet Door
21630-716	47 U	IP55	Black Grey	RAL 7021	4-Point Locking	Cabinet Door

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**