

Brass Plate



nVent PYROTENAX Brass Plate are a range of brass plates used to avoid induction heating of ferrous metal enclosures where single conductor cables pass through the wall of the enclosure. Available with various numbers of holes and hole sizes. Custom sizes available.

FEATURES

Simple to install

Reliable during long life: 30 year product warranty available

SPECIFICATIONS

Contact Material: Brass

Voltage Rating: 600 V max

Catalog Number		
6BP12		
3H01/2		
3H03/4		
4H01		
4H01-1/4		
4H03/4		
5BP1		

Catalog Number
5BP114
5BP12
5BP34
4H01/2
6HO1
6HO1-1/4
6HO3/4
8BP1
8BP114
8BP34
9BP1
9BP114
12BP34
16BP34
3HO1-1/4
1BP1
16BP114
2BP12

Catalog Number
2BP34
12BP114
3H01
10BP114

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com Asia Pacific

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com Latin America

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com