

Straight Through Joint



nVent PYROTENAX Straight Through Joint - NAM are a range of field installed, non fire-rated splice kits used to join MI copper-sheathed cables (with up to seven conductors), either where the manufactured length is shorter than the run length or for repair of damaged cables. If moisture is present, it must also be protected with a moisture protection kit.

FEATURES

Simple to install

Reliable during long life: 30 year product warranty available

SPECIFICATIONS

Voltage Rating: 600 V

Material: Brass

Table 1/1

Catalog Number	Max Operating Temperature	Suitable for Cable Type
STJ2/18-215T	221 °F	2/18-215T
STJ2/18-324TS	221 °F	2/18-324TS
STJ2/16-246T	221 °F	2/16-246T
STJ2/16-340	221 °F	2/16-340
STJ2/16-364TS	221 °F	2/16-364TS
STJ3/16-355	221 °F	3/16-355

Catalog Number	Max Operating Temperature	Suitable for Cable Type
STJ4/16-387	221 °F	4/16-387
STJ2/14-371	221 °F	2/14-371
STJ3/14-387	221 °F	3/14-387
STJ4/14-465	221 °F	4/14-465
STJ7/14-496	221 °F	7/14-496
STJ2/12-402	221 °F	2/12-402
STJ3/12-480	221 °F	3/12-480
STJ4/12-465	221 °F	4/12-465
STJ7/12-543	221 °F	7/12-543
STJ1/10-277	194 °F	1/10-277
STJ2/10-449	221 °F	2/10-449
STJ3/10-480	221 °F	3/10-480
STJ4/10-590	221 °F	4/10-590
STJ7/10-621	221 °F	7/10-621
STJ1/8-298	194 °F	1/8-298
STJ3/8-590	221 °F	3/8-590
STJ4/8-590	221 °F	4/8-590
STJ1/6-340	194 °F	1/6-340

Catalog Number	Max Operating Temperature	Suitable for Cable Type
STJ3/6-621	221 °F	3/6-621
STJ4/6-730	221 °F	4/6-730
STJ1/4-402	194 °F	1/4-402
STJ3/4-746	221 °F	3/4-746
STJ1/3-449	194 °F	1/3-449
STJ3/3-834	221 °F	3/3-834
STJ1/2-449	194 °F	1/2-449
STJ1/2-449/465	194 °F	1/2-449 to 465/1
STJ2/2-865	221 °F	2/2-865
STJ1/1-496	194 °F	1/1-496
STJ2/1-975	221 °F	2/1-975
STJ1/1/0-512	194 °F	1/1/0-512
STJ1/1/0-543/512	194 °F	1/1/0-512 to 543/1
STJ1/2/0-580	194 °F	1/2/0-580
STJ1/2/0-580/590	194 °F	1/2/0-580 to 590/1
STJ1/3/0-621	194 °F	1/3/0-621
STJ1/3/0-621/637	194 °F	1/3/0-621 to 637/1
STJ1/4/0-684	194 °F	1/4/0-684

Catalog Number	Max Operating Temperature	Suitable for Cable Type
STJ1/4/0-684/699	194 °F	1/4/0-684 to 699/1
STJ4/0-699/11/4	221 °F	699/1 (4/0)
STJ1/250-746	194 °F	1/250-746
STJ1/350-834	194 °F	1/350-834
STJ1/500-1000	194 °F	1/500-1000

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT