

On Demand Stock Panels: NGC-30



nVent RAYCHEM NGC-30 On Demand Stock Panels offer rapid delivery of optimized best-in-class standard panel configurations for customer projects. Panels are built with quality components including premium RAYCHEM controllers for use in hazardous and nonhazardous areas. Many configurations have C1D2 circuit breakers and Type 4X stainless steel enclosures.

FEATURES

Improve efficiency and reduce lead times by using standardized EHT controller & panel designs

Broad selection of configurations available immediately with best-in-class advanced control options

Consistent design with time-tested quality for your project

SPECIFICATIONS

Table 1/2

Catalog Number	Item Name	Main Circuit Breaker Current Rating	Touchscreen Included	Height	Width	Depth
10721-024	NGC-30-F-4X-H-20(1P)30A-277-80-N-0-T	80 A	Yes	60 in	36 in	16 in
10721-026	40ckt NGC30 EMR Z-PURGE 120V 30A-225A MB	225 A	Yes	72 in	36 in	24 in
10721-022	NGC-30-F-4X-H-40(1P)30A-277-175-N-0-T	175 A	Yes	72 in	48 in	24 in
10721-023	NGC-30-F-4X-H-30(1P)30A-277-125-N-0-T	125 A	Yes	72 in	48 in	24 in
10721-025	40ckt NGC30 EMR Z-PURGE 120V 24-16 30A	225 A	Yes	72 in	36 in	24 in

Table 2/2

Catalog Number	Item Name	Circuit Breaker Voltage Rating	Control Relay Type	Voltage Rating
10721-024	NGC-30-F-4X-H-20(1P)30A-277-80-N-0-T	277 V	Solid State	277 – 480 V
10721-026	40ckt NGC30 EMR Z-PURGE 120V 30A-225A MB	120 V	Electromechanical	120 – 208 V
10721-022	NGC-30-F-4X-H-40(1P)30A-277-175-N-0-T	277 V	Solid State	277 – 480 V
10721-023	NGC-30-F-4X-H-30(1P)30A-277-125-N-0-T	277 V	Solid State	277 – 480 V
10721-025	40ckt NGC30 EMR Z-PURGE 120V 24-16 30A	120 V	Electromechanical	120 – 208 V

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT