

FreezGard Self-Regulating Crankcase Heater



nVent RAYCHEM FreezGard self-regulating crankcase heater provide reliable peak heating during critical cold periods and, unlike constant wattage heaters, reduce their heat output once the compressor starts up or the air temperature rises.

FEATURES

Simple to design: available in 120 V and 208-277 V models

Easy to install: flexible lock-strap and prestripped 28-inch cold leads

Prolongs motor life

Increases compressor efficiency

SPECIFICATIONS

Nominal Height:0.245 inNominal Width:0.61 inCold Lead Length:28 ftLength:48 ftMax Intermittent Exposure Temperature, Power On:185 °FColor:BlackGround Path Type:Braid

Outer Jacket Material:Modified PolyolefinHeating Cable Technology:Self-Regulating

Table 1/1						
Catalog Number	Item Name	Nominal Voltage	Nominal Power Output @ 50°F, 120V	Nominal Power Output @ 50°F, 208V	Nominal Power Output @ 0°F, 120V	Nominal Power Output @ 0°F, 208V
864811-000	CCH-2C	208 V, 220 V, 240 V, 277 V		32 W		60 W
342903-000	CCH-1C	120 V	32 W		60 W	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com Asia Pacific

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com Latin America

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com