

FrostGuard Pipe Freeze Protection Hardwire Kit



nVent RAYCHEM FrostGuard pre-assembled self-regulating heating cables are designed for freeze protection applications. Available as 240 V, in various lengths with a 6 ft power cord.

FEATURES

Simple design

Pre-assembled heating cable with cold lead makes it easy to install

Energy efficient and safe

No overheating possible even when overlapped or closely spaced

Reliable during long life: 2 year product warranty available, maintenance free

SPECIFICATIONS

Min Installation Temperature:	5 °F
Cold Lead Length:	6 ft
Max Continuous Exposure Temperature, Power On:	150 °F
Supply Voltage:	208 – 240 V
Color:	Black
Ground Path Type:	Braid

Table 1/1

Catalog Number	Item Name	Nominal Power Output @ 40°F	Nominal Width	Nominal Height	Length
P000002029	FG2-6L	6 W/ft	0.45 in	0.24 in	6 ft
P000002030	FG2-12L	6 W/ft	0.45 in	0.24 in	12 ft
P000002031	FG2-18L	6 W/ft	0.45 in	0.24 in	18 ft

Catalog Number	Item Name	Nominal Power Output @ 40°F	Nominal Width	Nominal Height	Length
P000002032	FG2-24L	6 W/ft	0.45 in	0.24 in	24 ft

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
 Tel +1.800.545.6258
 Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa
 Tel +32.16.213.511
 Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific
 Tel +86.21.2412.1688
 Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America
 Tel +1.713.868.4800
 Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT