

Multiple-Entry Power/Tee Connection with Polymer Junction Box



nVent RAYCHEM JBM-100 is a modular junction box used to connect power to up to three nVent RAYCHEM BTV, QTVR, XTVR, HTV or VPL industrial parallel heating cables and integrates the functions of both connection kits and insulation entries. Offered in three versions, customized for local installation practices, each are also available with a power indicator. JBM-100-E, JBM-100-L-E; JBM-100-EP, JBM-100-L-EP; JBM-100-A, JBM-100-L-A.

FEATURES

Simple and fast to install, spacious boxes with front access, captive lid screws and robust spring type terminals for secure fixing

Part of a modular component system, providing maximum flexibility

One range for all nVent RAYCHEM industrial parallel heating cables

Simplified design in hazardous area, integral part of system approval

Cold-applied: core sealing boot with non-curing sealant; no heat gun, no hot work permit needed

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIONS

Max Conductor Cross Section: 0.0155 in²

For Ex-Zone Gas: 1, 2
Inlet Quantity: 2
Cable Entry: 3/4"
Connection Clamp Quantity: 6
For Ex-Zone Dust: 21, 22

Connection Type: Cold Applied

Material:Glass Fiber Reinforced PolymerArea Classification:Non-Hazardous; Hazardous

IP Rating: IP66
Knockouts Included: No
Mounting: On Pipe
Cover Attachment: Screwed

Table 1/2								
Catalog Number	Item Name	Ambient Temperature	Height	Width	Depth	Light Indication Included		
656081-000	JBM-100-L-A	-40 to 104 °F	9.4 in	8.6 in	3.5 in	Yes		
179935-000	JBM-100-A	-40 to 133 °F	9.4 in	8.6 in	3.5 in	No		
P000001376	JBM-100-A6	-40 to 133 °F	9.4 in	8.6 in	3.5 in	No		

Table 2/2								
Catalog Number	Item Name	Earth Plate Included	Modular	Below Insulation				
656081-000	JBM-100-L-A	No	No	No				
179935-000	JBM-100-A	No	No	No				
P000001376	JBM-100-A6	No	No	No				

ADDITIONAL PRODUCT DETAILS

Localized versions may exist with limited approvals and different part numbers. Contact your local sales representative.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com **Asia Pacific**

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com **Latin America**

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com