

WinterGard Self-Regulating Heating Cable



nVent RAYCHEM WinterGard self-regulating trace heating cables provide energy efficient and easy to use solutions for pipe freeze protection.

FEATURES

Simple to design

Easy to install: cut to length, meter marks

Energy efficient and safe: self regulating cable, advanced energy saving controls, no overheating possible

Reliable during long life: 2 year product warranty available, maintenance free

SPECIFICATIONS

Nominal Thickness: 0.18 in

Nominal Width: 0.38 in

Ground Path Type: Braid

Outer Jacket Material: None

Table 1/1

Catalog Number	Item Name	Nominal Voltage	Nominal Power Output @ 40°F, 120V	Nominal Power Output @ 40°F, 240V	Suitable for Pipe Size up to
064721-000	H311-250	120 V	3 W/ft		2 in
107153-000	H611-250	120 V	6 W/ft		6 in
330419-000	H621-050	240 V		6 W/ft	6 in
487817-000	H611-050	120 V	6 W/ft		6 in

Catalog Number	Item Name	Nominal Voltage	Nominal Power Output @ 40°F, 120V	Nominal Power Output @ 40°F, 240V	Suitable for Pipe Size up to
511569-000	H621-250	240 V		6 W/ft	6 in

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT