

WinterGard Self-Regulating Heating Cable, TruckPak



nVent RAYCHEM WinterGard self-regulating trace heating cables provide energy efficient and easy to use solutions for pipe freeze protection. This TruckPak kit includes heating cable, two H900 hardwired power/end seal kits, one H910 splice/tee kit, and one H903 application tape. Available as 120 V, 100 ft, 3W/ft or 6W/ft.

FEATURES

Energy efficient and safe: self regulating cable, advanced energy saving controls, no overheating possible

SPECIFICATIONS

Nominal Height:0.18 inNominal Width:0.38 inMax Continuous Exposure Temperature, Power On:150 °FGround Path Type:BraidOuter Jacket Material:None

Table 1/1					
Catalog Number	Item Name	Nominal Voltage	Nominal Power Output @ 40°F, 120V	Nominal Power Output @ 40°F, 240V	Suitable for Pipe Size up to
945417-000	H621-100	240 V		6 W/ft	6 in
192789-000	H611-100	120 V	6 W/ft		6 in
144941-000	H311-100	120 V	3 W/ft		2 in

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com Asia Pacific

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com Latin America

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com