


# **Assembly Parts for Rugged Components**



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

## **CERTIFICATIONS**



# **FEATURES**

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

## **SPECIFICATIONS**

**Product Type:** Assembly Kit **Product Family:** EuropacPRO

Table 1/2								
Catalog Number	Туре	Package Quantity	Thread Size	Finish	Material	Works With		
24566-105	Countersunk Screw	100	M4		Stainless Steel	Subracks		
24560-140	Square Nut	100		Zinc Plated	Steel	Subracks		
24566-106	Countersunk Screw	100	M4		Stainless Steel	Subracks		
24566-101	Countersunk Screw	100	M4		Stainless Steel	Subracks		

CatalogNumber	Туре	Package Quantity	Thread Size	Finish	Material	Works With
24566-100	Countersunk Screw	100	M4		Stainless Steel	Subracks
24566-104	Panhead Screw	100	M4		Stainless Steel	Subracks
24566-103	Panhead Screw	100	M4		Stainless Steel	Subracks
24566-102	Panhead Screw	100	M4		Stainless Steel	Subracks

Table 2/2					
Catalog Number	Quick Ship				
24566-105	No				
24560-140	No				
24566-106	No				
24566-101	No				
24566-100	No				
24566-104	No				
24566-103	No				
24566-102	No				

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

## Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

#### Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

#### Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE