


# ATCA Front Panel, Al-Profile, Reinforced With Spring Loading



AdvancedTCA front panel for spring-loaded IEA handle with die-cast end piece.

**CERTIFICATIONS** 



### **FEATURES**

Configuration: Front panel with IEA handle (with/without spring loading)

Al extrusion; for mesh EMC sealing


# **SPECIFICATIONS**

Rack Width: 6HP **Rack Height:** 8U

Material: Aluminum **Accessory Type:** Front panel **Product Type:** Front Panel

Table 1/1						
Catalog Number	Package Quantity	Handle Type	Front Finish	Rear Finish	Finish	Quick Ship
31596-900	1	Lever	Raw	Raw	Passivated	No
31596-899	1	Plunger	Raw	Raw	Passivated	No

## **DIAGRAMS**



### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

# Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

### Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

### Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE