

CompacPRO Desktop Case, Unshielded



The nVent SCHROFF CompacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frame and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

CERTIFICATIONS



FEATURES

Desktop case for individual assembly

Aluminum construction ensures robust solution

International dimensions in accordance with IEC 6297-3-101

Side panel with integrated handle function

Front and rear identical, depth-symmetrical construction

Ventilation slots in base plate

IP 20 in accordance with IEC 60529

SPECIFICATIONS

Product Type:	Case
Type:	Case for Individual Electronic Components
Product Family:	CompacPRO

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Front Frame Construction	Cooling Option	Complies With
----------------	-------------	------------	------------------	--------------------------	----------------	---------------

14575-023	2U	42HP	1	Single Piece	No	IEC 60297-3-103
14575-025	2U	42HP	1	Single Piece	No	IEC 60297-3-103
14575-027	2U	42HP	1	Single Piece	No	IEC 60297-3-103
14575-063	2U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-065	2U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-067	2U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-103	3U	28HP	1	Single Piece	No	IEC 60297-3-103
14575-105	3U	28HP	1	Single Piece	No	IEC 60297-3-103
14575-123	3U	42HP	1	Single Piece	No	IEC 60297-3-103
14575-125	3U	42HP	1	Single Piece	No	IEC 60297-3-103
14575-127	3U	42HP	1	Single Piece	No	IEC 60297-3-103
14575-143	3U	63HP	1	Single Piece	No	IEC 60297-3-103
14575-145	3U	63HP	1	Single Piece	No	IEC 60297-3-103
14575-147	3U	63HP	1	Single Piece	No	IEC 60297-3-103
14575-163	3U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-165	3U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-167	3U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-169	3U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-171	3U	84HP	1	Single Piece	No	IEC 60297-3-103

14575-223	4U	42HP	1	Single Piece	No	IEC 60297-3-103
14575-225	4U	42HP	1	Single Piece	No	IEC 60297-3-103
14575-243	4U	63HP	1	Single Piece	No	IEC 60297-3-103
14575-245	4U	63HP	1	Single Piece	No	IEC 60297-3-103
14575-247	4U	63HP	1	Single Piece	No	IEC 60297-3-103
14575-265	4U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-267	4U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-269	4U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-271	4U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-445	6U	63HP	1	Single Piece	No	IEC 60297-3-103
14575-447	6U	63HP	1	Single Piece	No	IEC 60297-3-103
14575-463	6U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-465	6U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-467	6U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-469	6U	84HP	1	Single Piece	No	IEC 60297-3-103
14575-471	6U	84HP	1	Single Piece	No	IEC 60297-3-103

Table 2/2

Catalog Number	EMC Shielding	Finish	Material	Protection Rating	Quick Ship
14575-023	No	Powder Coated	Aluminum	IP20	No
14575-025	No	Powder Coated	Aluminum	IP20	No

Catalog Number	EMC Shielding	Finish	Material	Protection Rating	Quick Ship
14575-027	No	Powder Coated	Aluminum	IP20	No
14575-063	No	Powder Coated	Aluminum	IP20	No
14575-065	No	Powder Coated	Aluminum	IP20	No
14575-067	No	Powder Coated	Aluminum	IP20	No
14575-103	No	Powder Coated	Aluminum	IP20	No
14575-105	No	Powder Coated	Aluminum	IP20	No
14575-123	No	Powder Coated	Aluminum	IP20	No
14575-125	No	Powder Coated	Aluminum	IP20	No
14575-127	No	Powder Coated	Aluminum	IP20	No
14575-143	No	Powder Coated	Aluminum	IP20	No
14575-145	No	Powder Coated	Aluminum	IP20	No
14575-147	No	Powder Coated	Aluminum	IP20	No
14575-163	No	Powder Coated	Aluminum	IP20	No
14575-165	No	Powder Coated	Aluminum	IP20	No
14575-167	No	Powder Coated	Aluminum	IP20	No
14575-169	No	Powder Coated	Aluminum	IP20	No
14575-171	No	Powder Coated	Aluminum	IP20	No
14575-223	No	Powder Coated	Aluminum	IP20	No

Catalog Number	EMC Shielding	Finish	Material	Protection Rating	Quick Ship
14575-225	No	Powder Coated	Aluminum	IP20	No
14575-243	No	Powder Coated	Aluminum	IP20	No
14575-245	No	Powder Coated	Aluminum	IP20	No
14575-247	No	Powder Coated	Aluminum	IP20	No
14575-265	No	Powder Coated	Aluminum	IP20	No
14575-267	No	Powder Coated	Aluminum	IP20	No
14575-269	No	Powder Coated	Aluminum	IP20	No
14575-271	No	Powder Coated	Aluminum	IP20	No
14575-445	No	Powder Coated	Aluminum	IP20	No
14575-447	No	Powder Coated	Aluminum	IP20	No
14575-463	No	Powder Coated	Aluminum	IP20	No
14575-465	No	Powder Coated	Aluminum	IP20	No
14575-467	No	Powder Coated	Aluminum	IP20	No
14575-469	No	Powder Coated	Aluminum	IP20	No
14575-471	No	Powder Coated	Aluminum	IP20	No

ADDITIONAL PRODUCT DETAILS

GND / earthing connections in accordance with

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE