

Filtered Door for RackChiller In-Row 45

CATALOG NUMBER

24630-188

The filtered door replaces a standard unfiltered door on the RackChiller In-Row 45 in order to extend the device with air filtering of incoming / warm aisle air. The filter is washable / cleanable with clean water or compressed air.

FEATURES

Filtration according to EN779:2012 Class G2; ISO 16890 Coarse 35%

Replaces standard door of RackChiller In-Row 45

PRODUCT ATTRIBUTES

Product Type: Air/Liquid Heat Exchanger

Product Family: Varistar

Color: Black Grey

Color Code: RAL 7021

Finish: Powder Coated

Material: Steel

Net Weight: 11.526kg

Package Quantity: 1

Rack Height: 42U

ADDITIONAL PRODUCT DETAILS

Works only with Varistar LHX+ 45 In-Rack and RackChiller In-Row 45

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE