


# Socket Strip, IEC C13, Metered

#### **CATALOG NUMBER**

# 60110-296









PDU with local power meter. Relevant Power data are shown on an integrated display.

#### **CERTIFICATIONS**





#### **FEATURES**

Socket strips can be rotated through all four directions (in 90° increments) during installation

Mounting height 1 U

Integrated measurement and display via local display unit

Socket strips with IEC 60320-C13 sockets

Horizontal and vertical mounting

#### PRODUCT ATTRIBUTES

Product Type: Socket Strip

Socket Type: IEC C13

t Type. ILO OT

Socket Quantity: 8

Color: Grey

Switched Outlets: Yes

Voltage AC: 230V

Material: Aluminum; Polyamide

Net Weight: 0.906kg

Package Quantity: 1

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

#### Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

## Asia

Shanghai, China

+86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE