


# EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded

EMC Shielded subrack for backplane mounting, heavy version with tox welded side panels.



## CERTIFICATIONS



## FEATURES

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

Rear horizontal rail for backplane mounting with insulation strip

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

IP 20, in accordance with IEC 60529

## SPECIFICATIONS

**Material:** Aluminum

**Finish:** Anodized; Passivated  
**Product Type:** Subrack/Chassis  
**EMC Shielding:** Yes

Table 1/2

Catalog Number	Rack Height	Package Quantity	Depth (D)	For Mounting	EMC Gasket Type	Shock and Vibration Tolerance
24563-172	3U	1	9.25in	Backplane	Textile	5g (force)
24563-173	3U	1	11.61in	Backplane	Textile	5g (force)
24563-174	3U	1	13.98in	Backplane	Textile	5g (force)
24563-472	6U	1	9.25in	Backplane	Textile	5g (force)
24563-473	6U	1	11.61in	Backplane	Textile	5g (force)
24563-474	6U	1	13.98in	Backplane	Textile	5g (force)

Table 2/2

Catalog Number	Handle Included	Mounting	Complies With	Rack Width	Quick Ship
24563-172	No	Rack	IEC 60297-3-103	84HP	No
24563-173	No	Rack	IEC 60297-3-103	84HP	No
24563-174	No	Rack	IEC 60297-3-103	84HP	No
24563-472	No	Rack	IEC 60297-3-103	84HP	No
24563-473	No	Rack	IEC 60297-3-103	84HP	No
24563-474	No	Rack	IEC 60297-3-103	84HP	No

## ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE