

# EuropacPRO 19" Subrack Kit for Backplane, Slide Rail, Retrofit Shielding



Non-shielded subrack for backplane, subrack can be assembled on slide rails to support the subrack inside a cabinet.

## CERTIFICATIONS



## FEATURES

Subrack with side panel type F ("Flexible"), 19" bracket is depth-adjustable

Subrack can be used with slide rails

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 11 kg

Threaded insert, insulation strip pre-fitted

## SPECIFICATIONS

<b>Material:</b>	Aluminum
<b>Finish:</b>	Anodized; Passivated
<b>EMC Shielding:</b>	No
<b>Product Type:</b>	Subrack/Chassis

Table 1/2

Catalog Number	Rack Height	Package Quantity	Depth	For Mounting	EMC Gasket Type	Handle Included
----------------	-------------	------------------	-------	--------------	-----------------	-----------------

24553-132	3U	1	9.25in	Backplane	Stainless Steel	No
24553-133	3U	1	11.61in	Backplane	Stainless Steel	No
24553-134	3U	1	13.98in	Backplane	Stainless Steel	No
24553-432	6U	1	9.25in	Backplane	Stainless Steel	No
24553-433	6U	1	11.61in	Backplane	Stainless Steel	No
24553-434	6U	1	13.98in	Backplane	Stainless Steel	No

Table 2/2

Catalog Number	Mounting	Complies With	Rack Width	Quick Ship
24553-132	Rack	IEC 60297-3-103	84HP	No
24553-133	Rack	IEC 60297-3-103	84HP	No
24553-134	Rack	IEC 60297-3-103	84HP	No
24553-432	Rack	IEC 60297-3-103	84HP	No
24553-433	Rack	IEC 60297-3-103	84HP	No
24553-434	Rack	IEC 60297-3-103	84HP	No

## ADDITIONAL PRODUCT DETAILS

Alternative product for older EuropacLab and Europac subrack series.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**