

EuropacPRO Advanced EMC Side Panel Covers for C-Profile Adaptors



Aluminium Side panel 3 mm to increase the EMC shielding effect of the subrack by increasing the material thickness and covering the not needed cut-outs. In this version specially prepared for the installation of an adapter for fixing the subrack with C-profile telescopic slides in a cabinet.

FEATURES

Side panel covers for increased lateral RF shielding, specially prepared for the installation of an adapter for fixing the subrack with C-profile telescopic slides in a cabinet

Assembled on the outside of the standard side panel

Assembly material included

Compatible C-profile adaptors can be found in the recommended accessory section

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Product Family	Type	Rack Height	Depth	EMC Shielding
24563-355	Side Panel	EuropacPRO	Type H	3U	6.89in	Yes
24563-356	Side Panel	EuropacPRO	Type H	3U	9.25in	Yes
24563-359	Side Panel	EuropacPRO	Type H	3U	11.61in	Yes
24563-360	Side Panel	EuropacPRO	Type H	3U	13.98in	Yes
24563-361	Side Panel	EuropacPRO	Type H	3U	16.34in	Yes
24563-362	Side Panel	EuropacPRO	Type H	3U	19.49in	Yes
24563-375	Side Panel	EuropacPRO	Type H	6U	6.89in	Yes

CatalogNumber	Product Type	Product Family	Type	Rack Height	Depth	EMC Shielding
24563-376	Side Panel	EuropacPRO	Type H	6U	9.25in	Yes
24563-379	Side Panel	EuropacPRO	Type H	6U	11.61in	Yes
24563-380	Side Panel	EuropacPRO	Type H	6U	13.98in	Yes
24563-381	Side Panel	EuropacPRO	Type H	6U	16.34in	Yes
24563-382	Side Panel	EuropacPRO	Type H	6U	19.49in	Yes

Table 2/2

Catalog Number	Material	Finish	Package Quantity	Package Unit	Quick Ship
24563-355	Aluminum	Passivated	2	Pair	No
24563-356	Aluminum	Passivated	2	Pair	No
24563-359	Aluminum	Passivated	2	Pair	No
24563-360	Aluminum	Passivated	2	Pair	No
24563-361	Aluminum	Passivated	2	Pair	No
24563-362	Aluminum	Passivated	2	Pair	No
24563-375	Aluminum	Passivated	2	Pair	No
24563-376	Aluminum	Passivated	2	Pair	No
24563-379	Aluminum	Passivated	2	Pair	No
24563-380	Aluminum	Passivated	2	Pair	No
24563-381	Aluminum	Passivated	2	Pair	No
24563-382	Aluminum	Passivated	2	Pair	No

ADDITIONAL PRODUCT DETAILS

Side panel and 19" bracket are tox-cold welded together. toxen = Clinching technique, without add aids. This takes place with special tools and high pressure.

Versions besides 3 and 6 U available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE