

Front Panel, Front Anodized, Rear Conductive, Unshielded

Front panel, unshielded, front anodized and rear conductive.



CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

SPECIFICATIONS

Material:	Aluminum
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel without Handle

Table 1/2

Catalog Number	Rack Height	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
30847-471	3U	1	Screw-on Front	Anodized	Conductive	No

CatalogNumber	Rack Height	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
30838-043	3U	1	Screw-on Front	Anodized	Conductive	No
30838-044	3U	1	Screw-on Front	Anodized	Conductive	No
30838-045	3U	1	Screw-on Front	Anodized	Conductive	No
30838-046	3U	1	Screw-on Front	Anodized	Conductive	No
30838-047	3U	1	Screw-on Front	Anodized	Conductive	No
30838-124	6U	1	Screw-on Front	Anodized	Conductive	No
30838-049	3U	1	Screw-on Front	Anodized	Conductive	No
30838-125	6U	1	Screw-on Front	Anodized	Conductive	No
30838-051	3U	1	Screw-on Front	Anodized	Conductive	No
30838-126	6U	1	Screw-on Front	Anodized	Conductive	No
30847-476	4U	1	Screw-on Front	Anodized	Conductive	No
30838-053	3U	1	Screw-on Front	Anodized	Conductive	No
30838-127	6U	1	Screw-on Front	Anodized	Conductive	No
30838-055	3U	1	Screw-on Front	Anodized	Conductive	No
30838-123	3U	1	Screw-on Front	Anodized	Conductive	No
30838-128	6U	1	Screw-on Front	Anodized	Conductive	No
30847-458	2U	1	Screw-on Front	Anodized	Conductive	No
30838-130	6U	1	Screw-on Front	Anodized	Conductive	No

CatalogNumber	Rack Height	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
30838-060	3U	1	Screw-on Front	Anodized	Conductive	No
30838-132	6U	1	Screw-on Front	Anodized	Conductive	No
30847-480	9U	1	Screw-on Front	Anodized	Conductive	No
30847-459	2U	1	Screw-on Front	Anodized	Conductive	No
30838-067	3U	1	Screw-on Front	Anodized	Conductive	No
30838-134	6U	1	Screw-on Front	Anodized	Conductive	No
30838-136	6U	1	Screw-on Front	Anodized	Conductive	No
30847-462	4U	1	Screw-on Front	Anodized	Conductive	No
30847-484	9U	1	Screw-on Front	Anodized	Conductive	No
30847-460	2U	1	Screw-on Front	Anodized	Conductive	No
30838-081	3U	1	Screw-on Front	Anodized	Conductive	No
30838-141	6U	1	Screw-on Front	Anodized	Conductive	No
30847-461	2U	1	Screw-on Front	Anodized	Conductive	No
30838-148	6U	1	Screw-on Front	Anodized	Conductive	No
30847-463	4U	1	Screw-on Front	Anodized	Conductive	No
30847-466	5U	1	Screw-on Front	Anodized	Conductive	No
30838-102	3U	1	Screw-on Front	Anodized	Conductive	No
30847-467	5U	1	Screw-on Front	Anodized	Conductive	No

CatalogNumber	Rack Height	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
30847-464	4U	1	Screw-on Front	Anodized	Conductive	No
30838-162	6U	1	Screw-on Front	Anodized	Conductive	No
30847-468	5U	1	Screw-on Front	Anodized	Conductive	No
30847-465	4U	1	Screw-on Front	Anodized	Conductive	No
30838-183	6U	1	Screw-on Front	Anodized	Conductive	No
30847-469	5U	1	Screw-on Front	Anodized	Conductive	No
30838-204	6U	1	Screw-on Front	Anodized	Conductive	No
30847-470	3U	1	Screw-on Front	Anodized	Conductive	No
30847-482	9U	1	Screw-on Front	Anodized	Conductive	No
30847-556	9U	1	Screw-on Front	Anodized	Conductive	No

Table 2/2

Catalog Number	Complies With	EMC Shielding	Certifications	Quick Ship
30847-471	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-043	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-044	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-045	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-046	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-047	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-124	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No

Catalog Number	Complies With	EMC Shielding	Certifications	Quick Ship
30838-049	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-125	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-051	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-126	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-476	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-053	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-127	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-055	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-123	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-128	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-458	IEC 60297-3-101, IEEE 1101.1/10	No		No
30838-130	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-060	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-132	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-480	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-459	IEC 60297-3-101, IEEE 1101.1/10	No		No
30838-067	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-134	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No


Catalog Number	Complies With	EMC Shielding	Certifications	Quick Ship
30838-136	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-462	IEC 60297-3-101, IEEE 1101.1/10	No		No
30847-484	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-460	IEC 60297-3-101, IEEE 1101.1/10	No		No
30838-081	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-141	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-461	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-148	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-463	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-466	IEC 60297-3-101, IEEE 1101.1/10	No		No
30838-102	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-467	IEC 60297-3-101, IEEE 1101.1/10	No		No
30847-464	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-162	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-468	IEC 60297-3-101, IEEE 1101.1/10	No		No
30847-465	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30838-183	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-469	IEC 60297-3-101, IEEE 1101.1/10	No		No

Catalog Number	Complies With	EMC Shielding	Certifications	Quick Ship
30838-204	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-470	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-482	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No
30847-556	IEC 60297-3-101, IEEE 1101.1/10	No	RoHS	No

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE