

# Front Panel, Unshielded, With Fastener Pin



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

## CERTIFICATIONS



## FEATURES

Enable grounding of the front area (protection class 1)

## SPECIFICATIONS

<b>Rack Height:</b>	3U
<b>Material:</b>	Aluminum
<b>Finish:</b>	Anodized; Passivated
<b>Accessory Type:</b>	Front panel
<b>Product Type:</b>	Front Panel
<b>Type:</b>	Front Panel without Handle

Table 1/2

Catalog Number	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
20119-159	7HP	1	Screw-on Front	Anodized	Conductive	No
20119-160	14HP	1	Screw-on Front	Anodized	Conductive	No

CatalogNumber	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
20119-161	21HP	1	Screw-on Front	Anodized	Conductive	No
20119-162	28HP	1	Screw-on Front	Anodized	Conductive	No
20119-163	42HP	1	Screw-on Front	Anodized	Conductive	No

Table 2/2

Catalog Number	Complies With	EMC Shielding	Quick Ship
20119-159	IEC 60297-3-101, IEEE 1101.1/10	No	No
20119-160	IEC 60297-3-101, IEEE 1101.1/10	No	No
20119-161	IEC 60297-3-101, IEEE 1101.1/10	No	No
20119-162	IEC 60297-3-101, IEEE 1101.1/10	No	No
20119-163	IEC 60297-3-101, IEEE 1101.1/10	No	No

## ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**