


# **Guide Rail End Piece, PC**





## **CERTIFICATIONS**



# **FEATURES**

Guide rail end pieces (PC) for individual multi-piece guide rails with plastic or aluminum extrusion mid-piece

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Mid-pieces available for standard PCB lengths (160, 220, 280 and 340 mm) and for special dimensions as 1000 mm version

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

# **SPECIFICATIONS**

Works With: Subracks; Cases; Chassis

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac

**Material:** Fiber-Reinforced Plastic

Product Type: Rail End Piece

Table 1/1								
<b>Catalog Number</b>	Package Quantity	<b>Complies With</b>	Туре	Package Unit	Quick Ship			

64568-018	1	EN 45545-2	Accessory	Pair	No
64568-004	1	EN 45545-2	Standard	Pair	No
64568-014	1	EN 45545-2	Standard	Pair	No
64568-093	1	EN 45545-2	Coding Peg	Pair	No
64568-094	1	EN 45545-2	Coding Peg	Pair	No
64568-095	1	EN 45545-2	Coding Peg	Pair	No
64568-008	1	EN 45545-2	Accessory	Pair	No

## ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

### **Europe**

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

# Asia

Shanghai, China

+86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

# Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF** TRACHTE