

LED Lights for Cabinets



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

CERTIFICATIONS



FEATURES

Lights can be easily mounted vertically or horizontally.

Simple through-wiring based on a plug-and-play system.

SPECIFICATIONS

Product Type: Light

Table 1/2

Catalog Number	Input Voltage AC	Accessory Type	Input Voltage DC	Package Quantity	Color	Finish
57274	250V max	Lights		1	Black	Smooth Matte
57275		Lights		2	Black	Smooth Matte
57265	230V max	Lights	24V max	1	Black	Smooth Matte
57272	250V max	Lights		1	Black	Smooth Matte

CatalogNumber	Input Voltage AC	AccessoryType	Input Voltage DC	Package Quantity	Color	Finish
57273	250V max	Lights		1	Black	Smooth Matte

Table 2/2

Catalog Number	Material	Type	Color Temperature	Nominal Voltage	Certifications	Quick Ship
57274	Plastic	Cabinet Light, Terminal Block		250V		No
57275		Cabinet Light, Magnet				No
57265	Plastic	Cabinet Light	5800K	230V	CE, RoHS	No
57272	Plastic	Connection Cable		250V		No
57273	Plastic	Cabinet Light		250V		No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE