

Monitor, Keyboard, Touchpad, 1 U Drawer, Reduced Depth



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFICATIONS



FEATURES

Pull-out 17" TFT color monitor chassis, 1 U (resolution Full HD; connects to VGA or DVI-D interface)

Keyboard with different keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 450 ... 640 mm

With DVI connection

SPECIFICATIONS

Product Type: Cabinet/Rack Drawer

Table 1/2

Catalog Number	Rack Height	Color	Color Code	Type	Works With	Keyboard Type
----------------	-------------	-------	------------	------	------------	---------------

60118-583	1U	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets	QWERTY UK
60118-584	1U	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets	QWERTZ
60118-585	1U	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets	AZERTY

Table 2/2

Catalog Number	Quick Ship
60118-583	No
60118-584	No
60118-585	No

ADDITIONAL PRODUCT DETAILS

Further versions on request – With trackball or numeric pad.

Other Keyboard layouts see user manual.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE