

MultipacPRO 19" Chassis, Aluminum, Plain Top and Base



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have plain top and bottom cover.

CERTIFICATIONS



FEATURES

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

SPECIFICATIONS

| | |
|------------------------|----------------------|
| Material: | Aluminum |
| Finish: | Anodized; Passivated |
| Product Family: | MultipacPRO |
| EMC Shielding: | No (Retrofittable) |
| Type: | Solid |

Product Type: Subrack/Chassis

Table 1/1

| Catalog Number | Rack Height | Mounting | Complies With | Certifications | Quick Ship |
|----------------|-------------|----------|-------------------------------------|----------------|------------|
| 20860-601 | 1U | Rack | IEC 60297-3-100, IEC 60297-3-105 | RoHS | No |
| 20860-602 | 1U | Rack | IEC 60297-3-100, IEC 60297-3-105 | RoHS | No |
| 20860-603 | 1U | Rack | IEC 60297-3-100 | | No |
| 20860-604 | 2U | Rack | IEC 60297-3-100 | | No |
| 20860-605 | 2U | Rack | IEC 60297-3-100 | RoHS | No |
| 20860-606 | 2U | Rack | IEC 60297-3-100 | RoHS | No |
| 20860-607 | 3U | Rack | IEC 60297-3-100 | RoHS | No |
| 20860-608 | 3U | Rack | IEC 60297-3-100 | RoHS | No |
| 20860-609 | 3U | Rack | IEC 60297-3-100 | RoHS | No |
| 20860-610 | 3U | Rack | IEC 60297-3-100 | | No |
| 20860-611 | 4U | Rack | IEC 60297-3-100 | | No |
| 20860-612 | 4U | Rack | IEC 60297-3-100 | RoHS | No |
| 20860-613 | 4U | Rack | IEC 60297-3-100 | RoHS | No |
| 20860-614 | 4U | Rack | IEC 60297-3-100 | RoHS | No |
| 20860-615 | 5U | Rack | IEC 60297-3-100 | RoHS | No |

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE