


Novastar Base/Plinth



Base Plate for Rear Cable Ducting which cut out for cable management. Opening is covered with plastic. Accessory brush strip can build in.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 400 kg

Adjustable feet, height 57 mm ... 67 mm

St, 1.5 mm, RAL 7021

Cable ducting 110 x 76 mm

Incl. GND/earthing

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Steel

Table 1/1								
Catalog Number	Package Quantity	Color	Color Code	Finish	Туре	Quick Ship		
27230-070	1	Black Grey	RAL 7021	Powder Coated	Base Plinth	No		
27230-080	1	Black Grey	RAL 7021	Powder Coated	Base Plinth	No		
27230-076	1	Black Grey	RAL 7021	Powder Coated	Base Plinth	No		
27230-072	1	Black Grey	RAL 7021	Powder Coated	Base Plinth	No		
27230-071	1	Black Grey	RAL 7021	Powder Coated	Base Plinth	No		

ADDITIONAL PRODUCT DETAILS

Please order brush strip separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

Nσ	۱rth	Δm	eri	ica

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE