


Novastar Mobile Plinth



Aluminum mobile base plinth with load capacity of 200 kg, for aluminum cabinets with 600 mm breadth.

CERTIFICATIONS



FEATURES

St, 2 mm

4 castors

Rubber mat, 3 mm

Load-carrying capacity 200 kg

Base/plinth height H = 100 mm

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Steel

Table 1/1										
Catalog Number	Package Quantity	Color	Color Code	Finish	Туре	Quick Ship				

27230-146	1	Black Grey	RAL 7021	Powder Coated	Base Plinth	No
27230-148	1	Black Grey	RAL 7021	Powder Coated	Base Plinth	No
27230-147	1	Black Grey	RAL 7021	Powder Coated	Base Plinth	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE