

Plug-In Unit Kit With IEL Handle, Shielded, Black, 3 U



Plug-in unit, with IEL inserter/extractor black handle, 3 U, front assembly. The U-shaped front panel enable shielding with a textile gasket.

CERTIFICATIONS



FEATURES

U-shaped front panel for textile gasket

Suitable for insertion and extraction forces up to 700 N (per pair)

Enable the installation of a microswitch

Enable the installation of coding pegs in accordance with IEC 60297-3-103/ IEEE 1101.10

SPECIFICATIONS

Material: Aluminum

Finish: Anodized; Passivated

Product Type: Front Panel


Type: Front Panel with Handle (PIU)

| Table 1/2 | | | | | | | |
|-------------------|------------|---------------------|-------------|----------|--------------------|--------------|--|
| Catalog Number | Rack Width | Package Quantity | Handle Type | Mounting | EMC Gasket Type | Front Finish | |

| 20848-585 | 4HP | 1 | IEL | Screw-on Front | Textile | Anodized |
|-----------|------|---|-----|----------------|---------|----------|
| 20848-589 | 8HP | 1 | IEL | Screw-on Front | Textile | Anodized |
| 20848-591 | 12HP | 1 | IEL | Screw-on Front | Textile | Anodized |
| 20848-587 | 6НР | 1 | IEL | Screw-on Front | Textile | Anodized |
| 20848-590 | 10HP | 1 | IEL | Screw-on Front | Textile | Anodized |

| Table 2/2 | | | | | | | |
|-------------------|-------------|---------------|---|---------------|-------------|------------|--|
| Catalog Number | Rear Finish | Treated Edges | Complies With | EMC Shielding | Rack Height | Quick Ship | |
| 20848-585 | Etched | No | IEC 60297-3- 102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | Yes | 3U | No | |
| 20848-589 | Etched | No | IEC 60297-3- 102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | Yes | 3U | No | |
| 20848-591 | Etched | No | IEC 60297-3- 102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | Yes | 3U | No | |
| 20848-587 | Etched | No | IEC 60297-3- 102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | Yes | 3U | No | |
| 20848-590 | Etched | No | IEC 60297-3- 102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | Yes | 3U | No | |

3U



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE