

# Plug-In Unit U-Profile Front Panel for XL Handle



Front panel for XL handle. Shieldable with textile gasket. with or without cutout for a microswitch.

#### **CERTIFICATIONS**



#### **FEATURES**

Al, front anodized, sides and rear conductive

Suitable for sleeve and collar screw

U-front profile, shieldable, for inserter/extractor handle, type XL

## **SPECIFICATIONS**

Material: Aluminum

Finish: Anodized; Passivated

Accessory Type: Front panel Product Type: Front Panel

**Type:** Front Panel for Handle (PIU)

**EMC Shielding:** No (Retrofittable)

Table 1/2							
Catalog Number	Rack Width	Package Quantity	Handle Type	Mounting	EMC Gasket Type	Front Finish	
30849-153	4HP	1	XL	Screw-on Front	Textile	Anodized	

CatalogNumber	Rack Width	Package Quantity	Handle Type	Mounting	EMC Gasket Type	Front Finish
30849-154	4HP	1	XL	Screw-on Front	Textile	Anodized
30849-156	8HP	1	XL	Screw-on Front	Textile	Anodized
30849-155	8HP	1	XL	Screw-on Front	Textile	Anodized
30849-158	12HP	1	XL	Screw-on Front	Textile	Anodized
30849-157	12HP	1	XL	Screw-on Front	Textile	Anodized


Table 2/2								
Catalog Number	Rear Finish	Treated Edges	Complies With	Rack Height	Quick Ship			
30849-153	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	6U	No			
30849-154	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	6U	No			
30849-156	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	6U	No			
30849-155	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	6U	No			
30849-158	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	6U	No			
30849-157	Conductive	No	IEC 60297-3-101, IEEE 1101.1/11	6U	No			


## **ADDITIONAL PRODUCT DETAILS**


Delivery is exclusively in standard pack quantity, Please order EMC textile gasket and microswitch separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

0 U/4 HP







## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

#### Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

#### Asia

Shanghai, China

+86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

#### Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**