

# PMC Mezzanine Front Panel, Untreated, With EMC Shielding



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments. For O-ring EMC gasket.

## CERTIFICATIONS



## FEATURES

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

## SPECIFICATIONS

**Product Type:** Front Panel  
**Type:** Front Panel without Handle  
**EMC Shielding:** Yes

Table 1/2

Catalog Number	Package Quantity	Accessory Type	Mounting	EMC Gasket Type	Front Finish	Rear Finish
20835-598	1	Front panel	Screw-on Front	O-ring	Anodized	Conductive
20835-889	1	Front panel	Screw-on Front	O-ring	Anodized	Conductive

CatalogNumber	Package Quantity	AccessoryType	Mounting	EMC Gasket Type	Front Finish	Rear Finish
20835-890	1		Screw-on Front			
20835-922	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-923	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-893	10		Screw-on Front		Chrome Plated	Chrome Plated
20835-924	10		Screw-on Front		Chrome Plated	Chrome Plated
20835-928	10		Screw-on Front		Anodized	Conductive

Table 2/2

Catalog Number	Treated Edges	Complies With	Finish	Material	Quick Ship
20835-598	No	PMC Mezzanine, IEEE P1386	Anodized	Aluminum	No
20835-889	No	PMC Mezzanine, IEEE P1386	Anodized	Aluminum	No
20835-890	No	PMC Mezzanine, IEEE P1386		Zinc	No
20835-922	Yes	PMC Mezzanine, IEEE P1386		Zinc	No
20835-923	Yes	PMC Mezzanine, IEEE P1386		Zinc	No
20835-893	Yes	PMC Mezzanine, IEEE P1386		Zinc	No
20835-924	Yes	PMC Mezzanine, IEEE P1386		Zinc	No
20835-928	No	PMC Mezzanine, IEEE P1386		Zinc	No

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**