


PropacPRO Desktop Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

CERTIFICATIONS



FEATURES

Desktop case for individual assembly

Ventilation slots in base plate

Retrofitable EMC shielding

Prepared for GND/earthing

Conforms with DIN EN 62368-1

SPECIFICATIONS

Product Type:	Case
Type:	Case for Individual Electronic Components
Product Family:	PropacPRO

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Front Frame Construction	Cooling Option	Complies With
14576-021	2U	42HP	1	Single Piece	No	IEC 60297-3-101

CatalogNumber	Rack Height	Rack Width	Package Quantity	Front Frame Construction	Cooling Option	Complies With
14576-023	2U	42HP	1	Single Piece	No	IEC 60297-3-101
14576-041	2U	63HP	1	Single Piece	No	IEC 60297-3-101
14576-043	2U	63HP	1	Single Piece	No	IEC 60297-3-101
14576-045	2U	63HP	1	Single Piece	No	IEC 60297-3-101
14576-101	3U	28HP	1	Single Piece	No	IEC 60297-3-101
14576-103	3U	28HP	1	Single Piece	No	IEC 60297-3-101
14576-121	3U	42HP	1	Single Piece	No	IEC 60297-3-101
14576-123	3U	42HP	1	Single Piece	No	IEC 60297-3-101
14576-125	3U	42HP	1	Single Piece	No	IEC 60297-3-101
14576-141	3U	63HP	1	Single Piece	No	IEC 60297-3-101
14576-143	3U	63HP	1	Single Piece	No	IEC 60297-3-101
14576-145	3U	63HP	1	Single Piece	No	IEC 60297-3-101
14576-161	3U	84HP	1	Single Piece	No	IEC 60297-3-101
14576-163	3U	84HP	1	Single Piece	No	IEC 60297-3-101
14576-165	3U	84HP	1	Single Piece	No	IEC 60297-3-101
14576-167	3U	84HP	1	Single Piece	No	IEC 60297-3-101
14576-169	3U	84HP	1	Single Piece	No	IEC 60297-3-101
14576-221	4U	42HP	1	Single Piece	No	IEC 60297-3-101

CatalogNumber	Rack Height	Rack Width	Package Quantity	Front Frame Construction	Cooling Option	Complies With
14576-223	4U	42HP	1	Single Piece	No	IEC 60297-3-101
14576-241	4U	63HP	1	Single Piece	No	IEC 60297-3-101
14576-243	4U	63HP	1	Single Piece	No	IEC 60297-3-101
14576-245	4U	63HP	1	Single Piece	No	IEC 60297-3-101
14576-247	4U	63HP	1	Single Piece	No	IEC 60297-3-101
14576-265	4U	84HP	1	Single Piece	No	IEC 60297-3-101
14576-267	4U	84HP	1	Single Piece	No	IEC 60297-3-101
14576-269	4U	84HP	1	Single Piece	No	IEC 60297-3-101
14576-463	6U	84HP	1	Single Piece	No	IEC 60297-3-101
14576-465	6U	84HP	1	Single Piece	No	IEC 60297-3-101
14576-467	6U	84HP	1	Single Piece	No	IEC 60297-3-101
14576-469	6U	84HP	1	Single Piece	No	IEC 60297-3-101

Table 2/2

Catalog Number	EMC Shielding	Finish	Material	Protection Rating	Quick Ship
14576-021	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-023	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-041	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-043	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-045	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No

Catalog Number	EMC Shielding	Finish	Material	Protection Rating	Quick Ship
14576-101	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-103	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-121	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-123	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-125	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-141	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-143	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-145	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-161	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-163	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-165	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-167	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-169	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-221	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-223	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-241	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-243	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-245	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No

Catalog Number	EMC Shielding	Finish	Material	Protection Rating	Quick Ship
14576-247	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-265	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-267	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-269	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-463	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-465	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-467	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No
14576-469	No (Retrofittable)	Passivated, Powder Coated	Aluminum	IP20	No

ADDITIONAL PRODUCT DETAILS

Case, 2 U with side panel for tip-up carrying handle on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE