

PSU 19" DC/DC Coolpower 100 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications.

CERTIFICATIONS



FEATURES

Wide input voltage range from 20 to 72 VDC

Galvanic separation between primary and secondary circuits

High power density

External ON/OFF

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Input Voltage DC	Power	Number of Output Voltages	Voltage 1	Current 1
13103-002	19" DC/DC Converter	20 – 72V	100W	1	5V	20A
13103-003	19" DC/DC Converter	20 – 72V	102W	1	12V	8.5A
13103-004	19" DC/DC Converter	20 – 72V	100W	1	15V	6.7A

Table 2/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
13103-002	3U	6HP	1	No
13103-003	3U	6HP	1	No
13103-004	3U	6HP	1	No

ADDITIONAL PRODUCT DETAILS

Please order front panel separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE