

Socket Strip With 2 Supply Cable, 3-Phase



Modular, compact PDU with two power cord inputs that can be connected to an A and B power feed. Space saving design in one chassis.

CERTIFICATIONS





FEATURES

Horizontal and vertical assembly possible

Two connector cables (halved in direction of length), 3 m (with open end), 2 x 3 phase, 400 VAC (red, black, white area)

Socket strips can be rotated in all directions (in 90° increments) during installation

Mounting height 1 U

SPECIFICATIONS

Material:Aluminum; PolyamideColor:Grey; Black; RedProduct Type:Socket Strip

Table 1/2							
Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Package Quantity	Finish	
60110-287	IEC C13	48	No	400V	1	Anodized	
60110-286	IEC C13, SCHUKO	36	No	400V	1	Anodized	

Table 2/2					
Catalog Number	Quick Ship				
60110-287	No				
60110-286	No				

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE