

Socket Strip With 2 Supply Cable, 3-Phase

Modular, compact PDU with two power cord inputs that can be connected to an A and B power feed. Space saving design in one chassis.



CERTIFICATIONS



FEATURES

Horizontal and vertical assembly possible

Two connector cables (halved in direction of length), 3 m (with open end), 2 x 3 phase, 400 VAC (red, black, white area)

Socket strips can be rotated in all directions (in 90° increments) during installation

Mounting height 1 U

SPECIFICATIONS

Material: Aluminum; Polyamide

Color: Grey; Black; Red

Product Type: Socket Strip

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Package Quantity	Finish
60110-286	IEC C13, SCHUKO	36	No	400V	1	Anodized
60110-287	IEC C13	48	No	400V	1	Anodized

Table 2/2

Catalog Number	Quick Ship
60110-286	No
60110-287	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE