


U-profile Front Panel, Shieldable, D-Sub Cutouts



U-profile front panel with cutout for D-Sub connectors. Shieldable for textile EMC gasket.

CERTIFICATIONS



FEATURES

U-profile, front panel, Al, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

SPECIFICATIONS

Rack Height: 3U Rack Width: 4HP

Material: Aluminum

Finish: Anodized; Passivated

Accessory Type: Front panel Product Type: Front Panel

Type: Front Panel without Handle

EMC Shielding: No (Retrofittable)

Table 1/2								
Catalog Number	Package Quantity	Mounting	EMC Gasket Type	Front Finish	Rear Finish	Number of Pins		
30849-751	1	Screw-on Front	Textile	Anodized	Conductive	(3) 9		
30849-750	1	Screw-on Front	Textile	Anodized	Conductive	(2) 9		
30849-752	1	Screw-on Front	Textile	Anodized	Conductive	(1) 15		
30849-754	1	Screw-on Front	Textile	Anodized	Conductive	(1) 25		
30849-753	1	Screw-on Front	Textile	Anodized	Conductive	(2) 15		
30849-755	1	Screw-on Front	Textile	Anodized	Conductive	(2) 25		
30849-749	1	Screw-on Front	Textile	Anodized	Conductive	(1) 9		

Table 2/2							
Catalog Number	Treated Edges	Complies With	Quick Ship				
30849-751	No	IEC 60297-3-101, IEEE 1101.1/10	No				
30849-750	No	IEC 60297-3-101, IEEE 1101.1/10	No				
30849-752	No	IEC 60297-3-101, IEEE 1101.1/10	No				
30849-754	No	IEC 60297-3-101, IEEE 1101.1/10	No				
30849-753	No	IEC 60297-3-101, IEEE 1101.1/10	No				
30849-755	No	IEC 60297-3-101, IEEE 1101.1/10	No				
30849-749	No	IEC 60297-3-101, IEEE 1101.1/10	No				

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please order textile EMC gasket separately.


47.5

7.45 20

ø3.1

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff

TRACHTE



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF