

Varistar CP Cabinet Frame, Seismic Heavy Load



Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

FEATURES

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded heavy-duty frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 500 kg to IEC 61587-2

SPECIFICATIONS

Product Type: Cabinet/Rack Frame

Frame Material: Steel

Table 1/2

Catalog Number	Rack Height	Package Quantity	Shock and Vibration Tolerance	Frequency	Color	Color Code
20630-273	33U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-274	33U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-275	33U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-276	33U	1	5g (force)	50 Hz	Black Grey	RAL 7021

CatalogNumber	Rack Height	Package Quantity	Shock and Vibration Tolerance	Frequency	Color	Color Code
20630-277	38U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-278	38U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-279	38U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-280	38U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-281	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-282	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-283	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-284	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-285	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-286	47U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-287	47U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-288	47U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-269	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-270	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-271	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-272	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021

Table 2/2

Catalog Number	Complies With	Finish	Material	Type	Works With	Quick Ship
----------------	---------------	--------	----------	------	------------	------------

20630-273	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-274	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-275	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-276	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-277	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-278	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-279	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-280	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-281	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-282	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-283	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-284	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-285	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-286	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-287	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-288	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-269	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
20630-270	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load		No
20630-271	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No

20630-272	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Heavy Load	Varistar CP	No
-----------	-----------------------------	---------------	-------	------------	-------------	----

ADDITIONAL PRODUCT DETAILS

Please order attachments and components separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE