

Varistar CP Cabinet Frame, Seismic



Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

FEATURES

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded seismic frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 250 kg to IEC 61587-2

SPECIFICATIONS

Product Type: Cabinet/Rack Frame

Frame Material: Steel

Table 1/2

Catalog Number	Rack Height	Package Quantity	Shock and Vibration Tolerance	Frequency	Color	Color Code
20630-358	33U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-359	33U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-360	33U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-361	33U	1	5g (force)	50 Hz	Black Grey	RAL 7021

CatalogNumber	Rack Height	Package Quantity	Shock and Vibration Tolerance	Frequency	Color	Color Code
20630-362	38U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-363	38U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-364	38U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-365	38U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-366	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-367	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-370	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-371	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-374	47U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-375	47U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-376	47U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-377	47U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-368	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-369	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-372	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021
20630-373	42U	1	5g (force)	50 Hz	Black Grey	RAL 7021

Table 2/2

Catalog Number	Complies With	Finish	Material	Type	Works With	Quick Ship
----------------	---------------	--------	----------	------	------------	------------

20630-358	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-359	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-360	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-361	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-362	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-363	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-364	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-365	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-366	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-367	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-370	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-371	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-374	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-375	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-376	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-377	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-368	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-369	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
20630-372	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No

20630-373	IEC 61587-1, IEC 61587-2	Powder Coated	Steel	Seismic	Varistar CP	No
-----------	-----------------------------	---------------	-------	---------	-------------	----

ADDITIONAL PRODUCT DETAILS

Please order attachments and components separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE