

Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

FEATURES

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load-carrying capacity 400 kg (mounted at decoration frame)

SPECIFICATIONS

Product Type: Cabinet
Cladding Color Code: RAL 7021
Frame Material: Steel

Table 1/2

Catalog Number	Rack Height	Frame Color	Frame Color Code	Cladding Material	Cladding Color	Package Quantity
10630-036	42U	Black Grey	RAL 7021	Steel	Black Grey	1
10630-035	42U	Black Grey	RAL 7021	Steel	Black Grey	1

CatalogNumber	Rack Height	Frame Color	Frame Color Code	Cladding Material	Cladding Color	Package Quantity
10630-033	38U	Black Grey	RAL 7021	Steel	Black Grey	1
10630-034	38U	Black Grey	RAL 7021	Steel	Black Grey	1

Table 2/2

Catalog Number	Complies With	Finish	Material	Quick Ship
10630-036	IEC 60297-3-100	Powder Coated	Steel	No
10630-035	IEC 60297-3-100	Powder Coated	Steel	No
10630-033	IEC 60297-3-100	Powder Coated	Steel	No
10630-034	IEC 60297-3-100	Powder Coated	Steel	No

ADDITIONAL PRODUCT DETAILS

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE