

Varistar CP EMC Shortened Door with Recessed Mounting Plate



Recessed connection plates are needed for connectors which don't protrude out of the plane of the cabinet

FEATURES

Intelligent cable management design with recessed connection plates

Door with lever handle with push button

Door opening angle 180°

Connection plate is 400 mm high

For recessed plate: Plate recessed by 40 mm

SPECIFICATIONS

Product Type:	Cabinet Door
Protection Rating:	IP55
Locking Type:	Multi Point Locking
Material:	Steel; Stainless Steel

Table 1/1

Catalog Number	Rack Height	Package Quantity	Finish	Quick Ship
21630-903	38U	1	Powder Coated	No
21630-904	38U	1	Powder Coated	No
21630-905	42U	1	Powder Coated	No

Catalog Number	Rack Height	Package Quantity	Finish	Quick Ship
21630-906	42U	1	Powder Coated	No
21630-907	47U	1	Powder Coated	No
21630-908	47U	1	Powder Coated	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE