

# Varistar CP Flat Top Cover Closed

Flat top cover for Varistar CP cabinets without cable entry zones.



## FEATURES

Flat top cover closed

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Top Cover  
**Color Code:** RAL 7021  
**Material:** Steel

Table 1/2

Catalog Number	Protection Rating	Package Quantity	Color	Finish	Type	Works With
21630-260	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-315		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-254	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-186		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-255	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-187		1	Black Grey	Powder Coated	Closed	Varistar CP

CatalogNumber	Protection Rating	Package Quantity	Color	Finish	Type	Works With
21630-256	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-188		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-128	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-189		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-257	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-192		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-258	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-193		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-259	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-194		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-131	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-195		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-570		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-571		1	Black Grey	Powder Coated	Perforated	Varistar CP
21630-572		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-573		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-574		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-577		1	Black Grey	Powder Coated	Closed	Varistar CP

CatalogNumber	Protection Rating	Package Quantity	Color	Finish	Type	Works With
21630-578		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-579		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-580		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-557	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-558	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-559	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-560	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-561	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-564	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-565	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-566	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-567	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-129	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-190		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-130	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-191		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-196		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-132	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP

CatalogNumber	Protection Rating	Package Quantity	Color	Finish	Type	Works With
21630-197		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-575		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-576		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-581		1	Black Grey	Powder Coated	Closed	Varistar CP
21630-582		1	Black Grey	Powder Coated	Perforated	Varistar CP
21630-133	IP20	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-562	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-563	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-568	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP
21630-569	IP55	1	Black Grey	Powder Coated	Closed	Varistar CP

Table 2/2

Catalog Number	Quick Ship
21630-260	No
21630-315	No
21630-254	No
21630-186	No
21630-255	No
21630-187	No
21630-256	No

Catalog Number	Quick Ship
21630-188	No
21630-128	No
21630-189	No
21630-257	No
21630-192	No
21630-258	No
21630-193	No
21630-259	No
21630-194	No
21630-131	No
21630-195	No
21630-570	No
21630-571	No
21630-572	No
21630-573	No
21630-574	No
21630-577	No
21630-578	No

Catalog Number	Quick Ship
21630-579	No
21630-580	No
21630-557	No
21630-558	No
21630-559	No
21630-560	No
21630-561	No
21630-564	No
21630-565	No
21630-566	No
21630-567	No
21630-129	No
21630-190	No
21630-130	No
21630-191	No
21630-196	No
21630-132	No
21630-197	No

Catalog Number	Quick Ship
21630-575	No
21630-576	No
21630-581	No
21630-582	No
21630-133	No
21630-562	No
21630-563	No
21630-568	No
21630-569	No

## ADDITIONAL PRODUCT DETAILS

---

Please purchase the grounding kit separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**