

Varistar CP Glazed Door With 1-Point Locking



Varistar CP Glass Door Single Point Locking for IP 20 applications.

FEATURES

St, 1.5 mm

Security glass, 6 mm

Key lock cover

Opening angle 180°

SPECIFICATIONS

Product Type: Cabinet Door

Material: Steel; Glass

Protection Rating: IP20

Table 1/2

Catalog Number	Rack Height	Locking Type	Package Quantity	Color	Color Code	Complies With
21630-392	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-393	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-394	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-395	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-481	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1

CatalogNumber	Rack Height	Locking Type	Package Quantity	Color	Color Code	Complies With
21630-482	24U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-483	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-484	29U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-485	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-396	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-486	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-397	33U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-487	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-398	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-488	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-399	38U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-489	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-016	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-490	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-018	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-491	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-017	42U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1
21630-492	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1

CatalogNumber	Rack Height	Locking Type	Package Quantity	Color	Color Code	Complies With
21630-019	47U	Single Point Locking	1	Black Grey	RAL 7021	IEC 61587-1

Table 2/2

Catalog Number	Finish	Type	Works With	Quick Ship
21630-392	Powder Coated	Glass Door	Varistar CP	No
21630-393	Powder Coated	Glass Door	Varistar CP	No
21630-394	Powder Coated	Glass Door	Varistar CP	No
21630-395	Powder Coated	Glass Door	Varistar CP	No
21630-481	Powder Coated	Glass Door	Varistar CP	No
21630-482	Powder Coated	Glass Door	Varistar CP	No
21630-483	Powder Coated	Glass Door	Varistar CP	No
21630-484	Powder Coated	Glass Door	Varistar CP	No
21630-485	Powder Coated	Glass Door	Varistar CP	No
21630-396	Powder Coated	Glass Door	Varistar CP	No
21630-486	Powder Coated	Glass Door	Varistar CP	No
21630-397	Powder Coated	Glass Door	Varistar CP	No
21630-487	Powder Coated	Glass Door	Varistar CP	No
21630-398	Powder Coated	Glass Door	Varistar CP	No
21630-488	Powder Coated	Glass Door	Varistar CP	No
21630-399	Powder Coated	Glass Door	Varistar CP	No

Catalog Number	Finish	Type	Works With	Quick Ship
21630-489	Powder Coated	Glass Door	Varistar CP	No
21630-016	Powder Coated	Glass Door	Varistar CP	No
21630-490	Powder Coated	Glass Door	Varistar CP	No
21630-018	Powder Coated	Glass Door	Varistar CP	No
21630-491	Powder Coated	Glass Door	Varistar CP	No
21630-017	Powder Coated	Glass Door	Varistar CP	No
21630-492	Powder Coated	Glass Door	Varistar CP	No
21630-019	Powder Coated	Glass Door	Varistar CP	No

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE