

Varistar CP Glazed Door With 3-Point Locking



Glazed door with 3 point locking allows stronger contact between door and the cabinet frame.

FEATURES

Glazed Door With 3-Point Locking, With Lock

Lever handle with key insert (2 keys)

Opening angle 180°

Security glass, 6 mm

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Locking Type: 3-Point Locking

Product Type: Cabinet Door

Material: Steel; Glass

Table 1/2

Catalog Number	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Complies With
21630-416	24U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-717	24U	IP55	1	Black Grey	RAL 7021	IEC 61587-1
21630-417	24U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-718	24U	IP55	1	Black Grey	RAL 7021	IEC 61587-1

CatalogNumber	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Complies With
21630-418	29U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-719	29U	IP55	1	Black Grey	RAL 7021	IEC 61587-1
21630-419	29U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-720	29U	IP55	1	Black Grey	RAL 7021	IEC 61587-1
21630-420	33U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-721	33U	IP55	1	Black Grey	RAL 7021	IEC 61587-1
21630-421	33U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-722	33U	IP55	1	Black Grey	RAL 7021	IEC 61587-1
21630-422	38U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-723	38U	IP55	1	Black Grey	RAL 7021	IEC 61587-1
21630-423	38U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-724	38U	IP55	1	Black Grey	RAL 7021	IEC 61587-1
21630-092	42U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-725	42U	IP55	1	Black Grey	RAL 7021	IEC 61587-1
21630-095	42U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-726	42U	IP55	1	Black Grey	RAL 7021	IEC 61587-1
21630-093	47U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-727	47U	IP55	1	Black Grey	RAL 7021	IEC 61587-1

CatalogNumber	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Complies With
21630-096	47U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-728	47U	IP55	1	Black Grey	RAL 7021	IEC 61587-1
21630-094	52U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-097	52U	IP20	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Catalog Number	Finish	Type	Works With	Quick Ship
21630-416	Powder Coated	Glass Door	Varistar CP	No
21630-717	Powder Coated	Glass Door	Varistar CP	No
21630-417	Powder Coated	Glass Door	Varistar CP	No
21630-718	Powder Coated	Glass Door	Varistar CP	No
21630-418	Powder Coated	Glass Door	Varistar CP	No
21630-719	Powder Coated	Glass Door	Varistar CP	No
21630-419	Powder Coated	Glass Door	Varistar CP	No
21630-720	Powder Coated	Glass Door	Varistar CP	No
21630-420	Powder Coated	Glass Door	Varistar CP	No
21630-721	Powder Coated	Glass Door	Varistar CP	No
21630-421	Powder Coated	Glass Door	Varistar CP	No
21630-722	Powder Coated	Glass Door	Varistar CP	No
21630-422	Powder Coated	Glass Door	Varistar CP	No

Catalog Number	Finish	Type	Works With	Quick Ship
21630-723	Powder Coated	Glass Door	Varistar CP	No
21630-423	Powder Coated	Glass Door	Varistar CP	No
21630-724	Powder Coated	Glass Door	Varistar CP	No
21630-092	Powder Coated	Glass Door	Varistar CP	No
21630-725	Powder Coated	Glass Door	Varistar CP	No
21630-095	Powder Coated	Glass Door	Varistar CP	No
21630-726	Powder Coated	Glass Door	Varistar CP	No
21630-093	Powder Coated	Glass Door	Varistar CP	No
21630-727	Powder Coated	Glass Door	Varistar CP	No
21630-096	Powder Coated	Glass Door	Varistar CP	No
21630-728	Powder Coated	Glass Door	Varistar CP	No
21630-094	Powder Coated	Glass Door	Varistar CP	No
21630-097	Powder Coated	Glass Door	Varistar CP	No

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE