

# Varistar CP IP 55 Cabinet



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP20 and IP55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

## **FEATURES**

Type of protection IP 55

Doors with 3-point locking and screw-fixed side panels

Static load-carrying capacity 1600 kg

Side and rear panels can be installed by one person

EN45545-2 fire safety Gaskets

## **SPECIFICATIONS**

Product Type: Cabinet
Protection Rating: IP55
Cladding Color Code: RAL 7021
Frame Material: Steel

Table 1/2								
Catalog Number	Rack Height	Frame Color	Frame Color Code	Cladding Material	Cladding Color	Туре		
10630-042	42U	Black Grey	RAL 7021	Steel	Black Grey	Steel Door, Plain		
10630-041	42U	Black Grey	RAL 7021	Steel	Black Grey	Steel Door, Glazed		

Table 2/2							
Catalog Number	Package Quantity	<b>Complies With</b>	Finish	Material	Quick Ship		

10630-042	1	IEC 60529, IEC 61587-1, IEC 60297-3-100	Powder Coated	Steel	No
10630-041	1	IEC 60529, IEC 61587-1, IEC 60297-3-100	Powder Coated	Steel	No

### ADDITIONAL PRODUCT DETAILS

Further dimensions and versions available on ServicePLUS IP 55. Please order base/plinth separately. For the assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

## Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

## Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE