

Varistar CP Mobile Base/Plinth



Mobile base/plinth to make a cabinet mobile.

FEATURES

Covers, St, 1.5 mm

Load-carrying capacity on casters 400 kg, on adjustable feet 1600 kg

Support, St, 3 mm

Color RAL 7021

Plinth height H = 103 mm, with feet adjustable from 126 to 134 mm

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Steel

Table 1/2						
Catalog Number	Package Quantity	Color	Color Code	Finish	Туре	Works With
21630-664	1	Black Grey	RAL 7021	Powder Coated	Base Plinth, Mobile	Varistar CP
21630-655	1	Black Grey	RAL 7021	Powder Coated	Base Plinth, Mobile	Varistar CP
21630-663	1	Black Grey	RAL 7021	Powder Coated	Base Plinth, Mobile	Varistar CP
21630-662	1	Black Grey	RAL 7021	Powder Coated	Base Plinth, Mobile	Varistar CP
21630-661	1			Powder Coated	Base Plinth, Mobile	Varistar CP
21630-658	1	Black Grey	RAL 7021	Powder Coated	Base Plinth, Mobile	Varistar CP
21630-657	1	Black Grey	RAL 7021	Powder Coated	Base Plinth, Mobile	Varistar CP
21630-656	1	Black Grey	RAL 7021	Powder Coated	Base Plinth, Mobile	Varistar CP

Table 2/2				
Catalog Number	Quick Ship			
21630-664	No			
21630-655	No			
21630-663	No			
21630-662	No			
21630-661	No			
21630-658	No			
21630-657	No			
21630-656	No			

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE