

Varistar CP Rear Panel with Mounting Plate, Shortened



Shortened rear panel with mounting plate now available as a complete SKU for better cable management.

FEATURES

Screw fixed, Robust and Single person mountable Side Panel

Height of connection plate 400 mm

The height of the rear panel is 400 mm less than the cabinet height

Interior galvanized

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Protection Rating: IP55

Material: Stainless Steel

Table 1/1

Catalog Number	Rack Height	Package Quantity	Finish	Quick Ship
21630-378	38U	1	Powder Coated	No
21630-379	38U	1	Powder Coated	No
21630-380	42U	1	Powder Coated	No
21630-381	42U	1	Powder Coated	No

Catalog Number	Rack Height	Package Quantity	Finish	Quick Ship
21630-382	47U	1	Powder Coated	No
21630-383	47U	1	Powder Coated	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE