

Varistar CP Rear Panel, Screw Fixed



Cabinets have rear panels well screwed to the frame to have maximum contact with the gasket.

FEATURES

Screw fixed, Robust and Single person mountable Side Panel

Rear panel without grounding kit

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Material: Steel

Table 1/2

Catalog Number	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Finish
21630-384	24U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-198	24U	IP55	1	Black Grey	RAL 7021	Powder Coated
21630-385	24U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-204	24U	IP55	1	Black Grey	RAL 7021	Powder Coated
21630-386	29U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-199	29U	IP55	1	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Finish
21630-387	29U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-205	29U	IP55	1	Black Grey	RAL 7021	Powder Coated
21630-388	33U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-200	33U	IP55	1	Black Grey	RAL 7021	Powder Coated
21630-389	33U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-206	33U	IP55	1	Black Grey	RAL 7021	Powder Coated
21630-390	38U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-201	38U	IP55	1	Black Grey	RAL 7021	Powder Coated
21630-391	38U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-207	38U	IP55	1	Black Grey	RAL 7021	Powder Coated
21630-122	42U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-202	42U	IP55	1	Black Grey	RAL 7021	Powder Coated
21630-125	42U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-208	42U	IP55	1	Black Grey	RAL 7021	Powder Coated
21630-123	47U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-203	47U	IP55	1	Black Grey	RAL 7021	Powder Coated
21630-126	47U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-209	47U	IP55	1	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Finish
21630-545	24U	IP55	1			Powder Coated
21630-546	24U	IP55	1			Powder Coated
21630-547	29U	IP55	1			Powder Coated
21630-548	29U	IP55	1			Powder Coated
21630-549	33U	IP55	1			Powder Coated
21630-550	33U	IP55	1			Powder Coated
21630-551	38U	IP55	1			Powder Coated
21630-552	38U	IP55	1			Powder Coated
21630-553	42U	IP55	1			Powder Coated
21630-554	42U	IP55	1			Powder Coated
21630-555	47U	IP55	1			Powder Coated
21630-556	47U	IP55	1			Powder Coated
21630-124	52U	IP20	1	Black Grey	RAL 7021	Powder Coated
21630-127	52U	IP20	1	Black Grey	RAL 7021	Powder Coated

Table 2/2

Catalog Number	Type	Works With	Quick Ship
21630-384	Rear Panel	Varistar CP	No
21630-198	Rear Panel	Varistar CP	No
21630-385	Rear Panel	Varistar CP	No

Catalog Number	Type	Works With	Quick Ship
21630-204	Rear Panel	Varistar CP	No
21630-386	Rear Panel	Varistar CP	No
21630-199	Rear Panel	Varistar CP	No
21630-387	Rear Panel	Varistar CP	No
21630-205	Rear Panel	Varistar CP	No
21630-388	Rear Panel	Varistar CP	No
21630-200	Rear Panel	Varistar CP	No
21630-389	Rear Panel	Varistar CP	No
21630-206	Rear Panel	Varistar CP	No
21630-390	Rear Panel	Varistar CP	No
21630-201	Rear Panel	Varistar CP	No
21630-391	Rear Panel	Varistar CP	No
21630-207	Rear Panel	Varistar CP	No
21630-122	Rear Panel	Varistar CP	No
21630-202	Rear Panel	Varistar CP	No
21630-125	Rear Panel	Varistar CP	No
21630-208	Rear Panel	Varistar CP	No
21630-123	Rear Panel	Varistar CP	No

Catalog Number	Type	Works With	Quick Ship
21630-203	Rear Panel	Varistar CP	No
21630-126	Rear Panel	Varistar CP	No
21630-209	Rear Panel	Varistar CP	No
21630-545	Rear Panel	Varistar CP	No
21630-546	Rear Panel	Varistar CP	No
21630-547	Rear Panel	Varistar CP	No
21630-548	Rear Panel	Varistar CP	No
21630-549	Rear Panel	Varistar CP	No
21630-550	Rear Panel	Varistar CP	No
21630-551	Rear Panel	Varistar CP	No
21630-552	Rear Panel	Varistar CP	No
21630-553	Rear Panel	Varistar CP	No
21630-554	Rear Panel	Varistar CP	No
21630-555	Rear Panel	Varistar CP	No
21630-556	Rear Panel	Varistar CP	No
21630-124	Rear Panel	Varistar CP	No
21630-127	Rear Panel	Varistar CP	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE