

# Varistar CP Seismic Base/Plinth

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.



## FEATURES

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Base

**Material:** Steel

Table 1/2

Catalog Number	Package Quantity	Color	Color Code	Complies With	Finish	Type
21630-110	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Base Plinth
21630-111	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Base Plinth
21630-112	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Base Plinth
21630-113	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Base Plinth

CatalogNumber	Package Quantity	Color	Color Code	Complies With	Finish	Type
21630-114	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Base Plinth
21630-115	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Base Plinth
21630-116	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Base Plinth
21630-117	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Base Plinth

Table 2/2

Catalog Number	Works With	Quick Ship
21630-110	Varistar CP	No
21630-111	Varistar CP	No
21630-112	Varistar CP	No
21630-113	Varistar CP	No
21630-114	Varistar CP	No
21630-115	Varistar CP	No
21630-116	Varistar CP	No
21630-117	Varistar CP	No

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**