

Varistar CP Side Panel, Screw-Fixed

Screw assembly side panel for Varistar CP cabinet.



FEATURES

Screw fixed, Robust and Single person mountable Side Panel

Side panel without grounding kit

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Table 1/2

Catalog Number	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Finish
21630-276	38U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-236	38U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-044	42U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-242	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-045	42U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-243	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-047	47U	IP20	2	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Finish
21630-249	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-048	47U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-250	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-078	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-079	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-081	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-082	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-927	24U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-928	24U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-929	29U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-930	29U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-931	33U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-932	33U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-933	38U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-934	38U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-261	24U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-221	24U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-262	24U	IP20	2	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Finish
21630-222	24U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-265	29U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-225	29U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-266	29U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-226	29U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-269	33U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-229	33U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-270	33U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-230	33U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-273	38U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-233	38U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-274	38U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-234	38U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-277	42U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-237	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-278	42U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-238	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-279	42U	IP20	2	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Finish
21630-239	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-280	42U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-240	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-043	42U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-241	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-281	47U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-244	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-282	47U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-245	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-283	47U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-246	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-284	47U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-247	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-046	47U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-248	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-465	24U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-466	24U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-467	29U	IP55	2	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Finish
21630-468	29U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-469	33U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-470	33U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-471	38U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-472	38U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-473	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-474	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-475	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-476	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-077	42U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-477	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-478	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-479	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-480	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-080	47U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-049	52U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-051	52U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-050	52U	IP20	2	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Rack Height	Protection Rating	Package Quantity	Color	Color Code	Finish
21630-263	24U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-223	24U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-224	24U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-264	24U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-267	29U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-227	29U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-268	29U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-228	29U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-271	33U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-231	33U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-272	33U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-232	33U	IP55	2	Black Grey	RAL 7021	Powder Coated
21630-275	38U	IP20	2	Black Grey	RAL 7021	Powder Coated
21630-235	38U	IP55	2	Black Grey	RAL 7021	Powder Coated

Table 2/2

Catalog Number	Material	Type	Quick Ship
21630-276	Steel	Side Panel, Screw Fixed	No
21630-236	Steel	Side Panel, Screw Fixed	No
21630-044	Steel	Side Panel, Screw Fixed	No

Catalog Number	Material	Type	Quick Ship
21630-242	Steel	Side Panel, Screw Fixed	No
21630-045	Steel	Side Panel, Screw Fixed	No
21630-243	Steel	Side Panel, Screw Fixed	No
21630-047	Steel	Side Panel, Screw Fixed	No
21630-249	Steel	Side Panel, Screw Fixed	No
21630-048	Steel	Side Panel, Screw Fixed	No
21630-250	Steel	Side Panel, Screw Fixed	No
21630-078	Steel	Side Panel, Screw Fixed	No
21630-079	Steel	Side Panel, Screw Fixed	No
21630-081	Steel	Side Panel, Screw Fixed	No
21630-082	Steel	Side Panel, Screw Fixed	No
21630-927	Steel	Side Panel, Screw Fixed	No
21630-928	Steel	Side Panel, Screw Fixed	No
21630-929	Steel	Side Panel, Screw Fixed	No
21630-930	Steel	Side Panel, Screw Fixed	No
21630-931	Steel	Side Panel, Screw Fixed	No
21630-932	Steel	Side Panel, Screw Fixed	No
21630-933	Steel	Side Panel, Screw Fixed	No

Catalog Number	Material	Type	Quick Ship
21630-934	Steel	Side Panel, Screw Fixed	No
21630-261	Steel	Side Panel, Screw Fixed	No
21630-221	Steel	Side Panel, Screw Fixed	No
21630-262	Steel	Side Panel, Screw Fixed	No
21630-222	Steel	Side Panel, Screw Fixed	No
21630-265	Steel	Side Panel, Screw Fixed	No
21630-225	Steel	Side Panel, Screw Fixed	No
21630-266	Steel	Side Panel, Screw Fixed	No
21630-226	Steel	Side Panel, Screw Fixed	No
21630-269	Steel	Side Panel, Screw Fixed	No
21630-229	Steel	Side Panel, Screw Fixed	No
21630-270	Steel	Side Panel, Screw Fixed	No
21630-230	Steel	Side Panel, Screw Fixed	No
21630-273	Steel	Side Panel, Screw Fixed	No
21630-233	Steel	Side Panel, Screw Fixed	No
21630-274	Steel	Side Panel, Screw Fixed	No
21630-234	Steel	Side Panel, Screw Fixed	No
21630-277	Steel	Side Panel, Screw Fixed	No

Catalog Number	Material	Type	Quick Ship
21630-237	Steel	Side Panel, Screw Fixed	No
21630-278	Steel	Side Panel, Screw Fixed	No
21630-238	Steel	Side Panel, Screw Fixed	No
21630-279	Steel	Side Panel, Screw Fixed	No
21630-239	Steel	Side Panel, Screw Fixed	No
21630-280	Steel	Side Panel, Screw Fixed	No
21630-240	Steel	Side Panel, Screw Fixed	No
21630-043	Steel	Side Panel, Screw Fixed	No
21630-241	Steel	Side Panel, Screw Fixed	No
21630-281	Steel	Side Panel, Screw Fixed	No
21630-244	Steel	Side Panel, Screw Fixed	No
21630-282	Steel	Side Panel, Screw Fixed	No
21630-245	Steel	Side Panel, Screw Fixed	No
21630-283	Steel	Side Panel, Screw Fixed	No
21630-246	Steel	Side Panel, Screw Fixed	No
21630-284	Steel	Side Panel, Screw Fixed	No
21630-247	Steel	Side Panel, Screw Fixed	No
21630-046	Steel	Side Panel, Screw Fixed	No

Catalog Number	Material	Type	Quick Ship
21630-248	Steel	Side Panel, Screw Fixed	No
21630-465	Steel	Side Panel, Screw Fixed	No
21630-466	Steel	Side Panel, Screw Fixed	No
21630-467	Steel	Side Panel, Screw Fixed	No
21630-468	Steel	Side Panel, Screw Fixed	No
21630-469	Steel	Side Panel, Screw Fixed	No
21630-470	Steel	Side Panel, Screw Fixed	No
21630-471	Steel	Side Panel, Screw Fixed	No
21630-472	Steel	Side Panel, Screw Fixed	No
21630-473	Steel	Side Panel, Screw Fixed	No
21630-474	Steel	Side Panel, Screw Fixed	No
21630-475	Steel	Side Panel, Screw Fixed	No
21630-476	Steel	Side Panel, Screw Fixed	No
21630-077	Steel	Side Panel, Screw Fixed	No
21630-477	Steel	Side Panel, Screw Fixed	No
21630-478	Steel	Side Panel, Screw Fixed	No
21630-479	Steel	Side Panel, Screw Fixed	No
21630-480	Steel	Side Panel, Screw Fixed	No

Catalog Number	Material	Type	Quick Ship
21630-080	Steel	Side Panel, Screw Fixed	No
21630-049	Steel	Side Panel, Screw Fixed	No
21630-051	Steel	Side Panel, Screw Fixed	No
21630-050	Steel	Side Panel, Screw Fixed	No
21630-263	Steel	Side Panel, Screw Fixed	No
21630-223	Steel	Side Panel, Screw Fixed	No
21630-224	Steel	Side Panel, Screw Fixed	No
21630-264	Steel	Side Panel, Screw Fixed	No
21630-267	Steel	Side Panel, Screw Fixed	No
21630-227	Steel	Side Panel, Screw Fixed	No
21630-268	Steel	Side Panel, Screw Fixed	No
21630-228	Steel	Side Panel, Screw Fixed	No
21630-271	Steel	Side Panel, Screw Fixed	No
21630-231	Steel	Side Panel, Screw Fixed	No
21630-272	Steel	Side Panel, Screw Fixed	No
21630-232	Steel	Side Panel, Screw Fixed	No
21630-275	Steel	Side Panel, Screw Fixed	No
21630-235	Steel	Side Panel, Screw Fixed	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE